



YAV2CL2NTCFX

By Burndy
Catalog # [YAV2CL2NTCFX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.



Application

Wire Termination

General

Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810044582
UPC 12 Digit	7818100445822

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	103 mm
Dimension - Length Overall inch	4.07 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper Str Navy Size	60
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Str Size Range	2 AWG
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Status	
UL Listed	Yes

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SE...208119-01](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV2CL2NTCFX-SPEC-EN | REV 6/2023