



B2E12N Flexible Copper Braid

By Burndy
Catalog # [B2E12N](#)

Cu Flexible Braid, 2-NEMA Holes 2 Ferrules, 12.00" L, 0.56" Hole Dia, 2 Braids, Amp Rating: 530 Indoor, 635 Outdoor.



General

Catalog Number	B2E12N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810004890
UPC 12 Digit	7818100048900

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.62 in
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
- [Sales Drawings - SE210201-02_DI](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-B2E12N-SPEC-EN | REV 6/2024