



# BG18 Flexible Copper Braid, 18 in L

By Burndy  
Catalog # BG18

Flexible Copper Braid, 18 in L.



## General

Application	Flexible copper braid jumpers designed to take up linear expansion and contraction
Catalog Number	BG18
Connector Type	Braid
EU RoHS Indicator	Yes
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID
Type	B, Flexible
UPC	781810005156
UPC 12 Digit	7818100051566

## Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.50 in
Length	18 in

## Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)
- [Sales Drawings - SE..210201-01](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-BG18-SPEC-EN | REV 6/2024