



# BD18G163TN

By Burndy  
Catalog # [BD18G163TN](#)

Flexible Tin Copper Braid 18 inches long.



## General

Catalog Number	BD18G163TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810475683
UPC 12 Digit	7818104756833

## Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in

## Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

## Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30018574](#)
- [Specifications - BD18G163TN Specification Sheet French](#)