



B2G11D50G142SV

By Burndy
Catalog # B2G11D50G142SV

Flexible tinned copper braid 12.50"x1.38"x0.38".

General

Catalog Number	B2G11D50G142SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	2
UPC	781810548851
UPC 12 Digit	7818105488511

Dimensions

Dimension - L Length Overall mm	292
Dimension - Length Overall inch	11.5
Dimension - Width inch	1.5
Dimension - Width mm	38 mm

Electrical Ratings

Rating - Indoor Amperage	700 A
Rating - Outdoor Amperage	840 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2G11D50G142SV Specification Sheet French](#)