



B3D12N Flexible Copper Braid

By Burndy
Catalog # [B3D12N](#)

Cu Flexible Braid Jumper, 3 Braids in Ferrules, 2 Holes 2 Ferrules, 1.75" Spacing, 12.00" L, .56" Hole Dia., Amp Rating: 470(Indoor) 560(Outdoor).



General

Catalog Number	B3D12N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810004944
UPC 12 Digit	7818100049444

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	470
Rating - Outdoor Amperage	560

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
- [Sales Drawings - SE210201-02_DI](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-B3D12N-SPEC-EN | REV 6/2024