

GL2929T4, Mechanical Ground Connector, 2 Copper Cables to Bar

By Burndy
Catalog # [GL2929T4](#)



Cast Cu Alloy Ground Clamp, 2 Cables to Bar, 2/0 AWG Sol - 250 Kcmil Cu, 1/2" - 1/4" Bar Thickness.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

General

Catalog Number	GL2929T4
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810117415
UPC 12 Digit	7818101174155

Dimensions

Dimension - B Length inch	2.22 in
Dimension - D inch	2.25 in
Dimension - F Width Center to Center inch	1.25 in
Dimension - Height mm	0 mm
Dimension - Length Side B inch	2.44 in
Dimension - Pad Width inch	1.22 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_glla](#)
[Sales Drawings - sc011810-01](#)
[Specifications - GL2929T4 Specification Sheet French](#)