



BE24D60G201

By Burndy
Catalog # [BE24D60G201](#)

Flexible Copper Braid.



General

Catalog Number	BE24D60G201
Connector Type	Braid
Material	Copper
UPC	781810637265
UPC 12 Digit	7818106372655

Dimensions

Dimension - L Length Overall mm	625 mm
Dimension - Length Overall inch	24.60 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BE24D60G201 Specification Sheet French](#)



A Hubbell brand