



B2F12G119TN

By Burndy
Catalog # B2F12G119TN

Flexible tinned copper braid 12.00"x1.38"x0.38".



General

Catalog Number	B2F12G119TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810563625
UPC 12 Digit	7818105636255

Dimensions

Dimension - L Length Overall mm	305
Dimension - Length Overall inch	12
Dimension - Width inch	1.38
Dimension - Width mm	35 mm

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2F12G119TN Specification Sheet French](#)



A Hubbell brand