



Ratchet Cable Cutter, Cuts up to 600 kcmil Soft Drawn Copper and Aluminum, Maximum Insulation Diameter 1.05"

By Burndy
Catalog # [RCC600E](#)



Ratchet Cable Cutter, Cuts up to 600 kcmil Soft Drawn CU/AL, Max. Ins Dia. 1.05".

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	RCC600E
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810488195
UPC 12 Digit	7818104881955

Dimensions

Cable Insulation Diameter Maximum	1.05 in
Length	10.5 in
Weight	1.2 lb
Width	1.25 in

Conductor Related

Crimping Ranges Cutting Capacity: Copper 600 kcmil; Aluminum: 600 kcmil

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - BUR_30015047_SOMI_RCC600E](#)
[Sales Drawings - 30017058](#)



A proud member of the Hubbell Family.