



BD12T14

By Burndy
Catalog # [BD12T14](#)

Flexible Tin Copper Braid 12 inches long.



General

Catalog Number	BD12T14
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	621945433441
UPC 12 Digit	6219454334411

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Logistics

Carton Quantity	50
Pallet Quantity	4800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50007530](#)
- [Specifications - BD12T14 Specification Sheet French](#)



A Hubbell brand