



BD16G249TN

By Burndy  
Catalog # [BD16G249TN](#)

Tin Plated Ferrules.



General

Catalog Number	BD16G249TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin plated
UPC	781810426333
UPC 12 Digit	7818104263333

Dimensions

Dimension - Hole Size inch	0.38 in
Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16 in
Dimension - Pad Width inch	0.94 in
Thickness	0.13 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BD16G249TN Specification Sheet French](#)



A Hubbell brand