



BE12G149

By Burndy
Catalog # [BE12G149](#)

Flexible Copper Braid.



General

| | |
|---------------------------------------|---------------|
| Catalog Number | BE12G149 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| UPC | 781810363454 |
| UPC 12 Digit | 7818103634544 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12.00 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 340 |
| Rating - Outdoor Amperage | 405 |

Certifications And Compliance

| | |
|---|-------|
| Certification - UL Listed Direct Burial | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BE12G149 Specification Sheet French](#)