



# B3G11D50G66SV

By Burndy  
Catalog # B3G11D50G66SV

Flexible tinned copper braid 11.50"x0.75".



## General

Catalog Number	B3G11D50G66SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	3
UPC	781810548844
UPC 12 Digit	7818105488444

## Dimensions

Dimension - L Length Overall mm	292
Dimension - Length Overall inch	11.5
Dimension - Width inch	0.75
Dimension - Width mm	19 mm

## Electrical Ratings

Rating - Indoor Amperage	960 A
Rating - Outdoor Amperage	1150 A

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B3G11D50G66SV Specification Sheet French](#)