



# BD24G127

By Burndy  
Catalog # [BD24G127](#)

Flexible Tin Copper Braid 24 inches long.



## General

Catalog Number	BD24G127
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Plating Type	Tin
UPC	781810443064
UPC 12 Digit	7818104430644

## Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in

## Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

## Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30018577](#)
- [Specifications - BD24G127 Specification Sheet French](#)