



B33G14G40TN

By Burndy
Catalog # B33G14G40TN

Flexible Tinned Copper Braid 14 X 4 X 0.87.



General

Catalog Number	B33G14G40TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	9
UPC	781810510544
UPC 12 Digit	7818105105444

Dimensions

Dimension - L Length Overall mm	356
Dimension - Length Overall inch	14
Dimension - Width inch	4
Dimension - Width mm	102 mm

Electrical Ratings

Amperage Rating	3000 A
-----------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B33G14G40TN Specification Sheet French](#)



A Hubbell brand