



BE25G155TN

By Burndy
Catalog # BE25G155TN

Tin Plated Ferrules.



General

Catalog Number	BE25G155TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810480724
UPC 12 Digit	7818104807244

Dimensions

Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25.00 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- Catalogs - [BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - BE25G155TN Specification Sheet French](#)