



B22F244N Flexible Copper Braid

By Burndy

Catalog # [B22F244N](#)

Flexible Copper Braid.



General

Catalog Number	B22F244N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	621945333628
UPC 12 Digit	6219453336288

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in
Length	24 in

Electrical Ratings

Rating - Outdoor Amperage	1100 A
---------------------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - se212603-01](#)



A Hubbell brand