



B2D15G84

By Burndy
Catalog # [B2D15G84](#)

Flexible Copper Braid.



General

Catalog Number	B2D15G84
Connector Type	Braid
Material	Copper
UPC	781810542828
UPC 12 Digit	7818105428288

Dimensions

Dimension - Hole Size inch	0.44
Dimension - L Length Overall mm	381
Dimension - Length Overall inch	15
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2D15G84 Specification Sheet French](#)