



BD18G80 18 inch Flexible Copper Braid

By Burndy
Catalog # [BD18G80](#)

Flexible Tin Copper Braid 18 inches long



General

Catalog Number	BD18G80
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Plating Type	Tin
UPC	781810199800
UPC 12 Digit	7818101998000

Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	4800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50047629](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BD18G80-SPEC-EN | REV 6/2024