



circular conduc. terminal TA4.4 4 x 4/0...600 kcmil for 4 cables; 3 units accessory for: 3VA55; 3VA65/3VA66

Model	
product brand name	SETRON
product designation	Circular conductor terminal, 4 cables, external, 3 units
accessories	Wire connector
General technical data	
designation / of the terminal	TA4.4
type of electrical connection / with control wire tap	No
Connections according IEC	
connectable conductor cross-section	
<ul style="list-style-type: none"> <li>for copper cable / stranded / minimum</li> <li>for copper cable / stranded / maximum</li> <li>for aluminum cable / stranded / minimum</li> <li>for aluminum cable / stranded / maximum</li> </ul>	120 mm <sup>2</sup> 300 mm <sup>2</sup> 120 mm <sup>2</sup> 300 mm <sup>2</sup>
stripped length	28,7 / 56,1 mm
tightening torque / when using copper cables	
<ul style="list-style-type: none"> <li>stranded</li> <li>finely stranded</li> </ul>	120 - 300 mm <sup>2</sup> : 42.4 Nm 150 ... 185 mm <sup>2</sup> 42.4 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C
stripped length	1.13 / 2.21 in
connectable conductor cross-section	
<ul style="list-style-type: none"> <li>for copper cable / stranded / minimum</li> <li>for copper cable / stranded / maximum</li> <li>for aluminum cable / stranded / minimum</li> <li>for aluminum cable / stranded / maximum</li> </ul>	4/0 AWG 600 kcmil 4/0 AWG 600 kcmil
Certificates	
General Product Approval	



[Miscellaneous](#)



EMV

Test Certificates

Marine / Shipping

other



[Type Test Certificates/Test Report](#)



[Miscellaneous](#)

[Confirmation](#)

[Miscellaneous](#)

## Environment

[Environmental Confirmations](#)

[Environmental Confirmations](#)

## Further information

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9673-0JJ44>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9673-0JJ44>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9673-0JJ44](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9673-0JJ44)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/27/2024

