



ECF-38 - 1" Flexible Coupling with 8" Bend Length, Bronze

By Killark
Catalog # [ECF-38](#)

1" Flexible Coupling with 8" Bend Length, Bronze.



*Representative Image

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

General

Catalog Number	ECF-38
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Bronze
Series	ECF
Type	Flexible Coupling
UPC	783936104355

Dimensions

Dimensions	14 in x 2.5 in x 2.5 in
Gross Weight with Packaging	3.63
Height	2.5 in
Hub Size	1"
Length	14 in
Width	2.5 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)
- [Specifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)
- [Specifications - ECF-38 Specification Sheet French](#)