



G Series - Long Momentary Contact Single Push Button Operator -Red Button With "Start"/"Stop" Nameplate - 1NC Contact Rating

By Killark
Catalog # [GO1-RX2B N34](#)



*Representative Image

G Series - Aluminum Long Momentary Contact Single Push Button Operator -Red Button With "Start"/"Stop" Nameplate - 1NC Contact Rating.

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

General

Action	Momentary
Actuator	Single Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GO1-RX2B N34
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Series	GO
UPC	783936221502

Dimensions

Dimensions	2.25 in x 6.625 in x 1.75 in
Gross Weight with Packaging	0.58
Height	1.75 in
Length	2.25 in
Width	6.625 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A

INRUSH @ 250 VDC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 0.55A BREAKING @ 125 VDC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC; 10A CARRYING @ 600 VAC; 2.5A CARRYING @ 125 VDC; 2.5A CARRYING @ 250 VDC.

Frequency Rating
50/60 Hz

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - G Series Auxiliary Devices UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - GO1 & GOL1 Single Pushbutton Operators IOM K1001](#)
- [Specifications - GO1-RX2B N34 Specification Sheet French](#)
- [Specifications - G Series Push Buttons Specification Sheet](#)