



KQS-250 ML - CELOX™ 250ml Killark Quick Sealing Compound With Four Static Mixing Nozzles



By Killark
Catalog # [KQS-250 ML](#)

CELOX™ 250ml Killark Quick Sealing Compound With Four Static Mixing Nozzles.

Features

- 250ml cartridge comes in a single barrel with a 2 chamber internal compartment that allows for more compact storing and use
- Two part epoxy resin is pushed through a patented static mixing wedge
- Each cartridge comes with 4 patented static mixing nozzles to form a perfect mix
- Cartridge dispensing guns and spare nozzles are available as ordering options

General

Catalog Number	KQS-250 ML
EU RoHS Indicator	Contact Manufacturer
Series	Celox
UPC	783936155319

Certifications And Compliance

Hazardous Rating(s)

- Class I, Division 1 & 2, Groups A, B, C, D
- Class II, Division 1 & 2, Groups E, F, G
- Class III, Division 1 & 2

Product Assets

- [Brochures - EZ Seal Next Generation of Hazardous-Rated Seal Fittings](#)
- [Brochures - Celox Gen II](#)
- [Catalog Page - EZ Series The Next Generation of Vertical Seal Fittings](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - ENY Series & Sealing Compound CSA Certificate](#)
- [Installation Manuals - KQS Series Celox IOM K1513](#)
- [SDS - Killark Celox Part B Curing Agent SDS](#)
- [SDS - Killark Celox Part A Resin SDS](#)
- [Specifications - KQS-250 ML Specification Sheet French](#)
- [Specifications - Celox - Killark Quick Seal Specification Sheet](#)
- [Video - Celox Gen II](#)