



## OL-45-RG - 1½" Neoprene O series Cover Gasket

By Killark  
Catalog # [OL-45-RG](#)

1½" Neoprene O series Cover Gasket.



\*Representative Image

### Application

For use with O Series fittings.

### General

Catalog Number	OL-45-RG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Material	Neoprene
Series	O Series
Type	Gasket
UPC	783936490113

### Dimensions

Dimensions	10.12 in x 4.68 in x 7.062 in
------------	-------------------------------

Gross Weight with Packaging	0.04
Height	7.062 in
Hub Size	1-1/4" to 1-1/2"
Length	10.12 in
Weight	0.16 lb
Width	4.68 in

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Specifications - OL-45-RG Specification Sheet French](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)