



OLR-5 - 1-1/2" LR Hub, Aluminum O Series Conduit Body

By Killark
Catalog # [OLR-5](#)

1-1/2" LR Hub, Aluminum O Series Conduit Body.



*Representative Image

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OLR-5
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LR
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body
UPC	783936490557

Dimensions

Dimensions	10.25 in x 5 in x 3.125 in
Gross Weight with Packaging	1.41
Height	3.125 in
Hub Size	1-1/2"
Length	10.25 in
Width	5 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [3D Models - OLR-5 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OLR-5 Engineering Drawing](#)
- [Sales Drawings - OLR-5 Sales Drawing](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLR-5 Specification Sheet French](#)