



UGP Series - 20 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 5-20P

By Killark
Catalog # [UGP-20231QW](#)



*Representative Image

UGP Series - Aluminum 20 Amp 125VAC Interchangeable Blade Style Plug With Quick Wiring - NEMA Configuration 5-20P.

General

Catalog Number	UGP-20231QW
Color	
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	UGP
Type	
UPC	783936076669

Dimensions

Dimensions	6.625 in x 2.375 in x 1.875 in
Gross Weight with Packaging	0.4
Height	1.875 in
Length	6.625 in
Width	2.375 in

Electrical Ratings

Amperage Rating	20 A
-----------------	------

Conductor Related

Number Of Wires	3
Wire Size	#10 AWG, #12 AWG, or #14 AWG

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">Class I, Divisions 1 & 2, Groups C, DClass I, Zones 1 & 2, Groups IIB, IIAClass II, Divisions 1 & 2, Groups F, GClass III, Divisions 1 & 2
Nema Rating	3, 4, 4X

Product Assets

- [Certifications - UGR/UGP Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - UGP-20231QW Engineering Drawing](#)
- [Installation Manuals - UGP Series IOM K1377](#)
- [Sales Drawings - UGP-20231QW Sales Drawing](#)
- [Specifications - UGP-20231QW](#)
- [Specifications - UGR & UGP Series Plugs & Receptacles Specification Sheet](#)