

# Eaton TRAF15W

Catalog Number: TRAF15W

Eaton slim AFCI receptacle, visual trip indicator light, 15 A, 125 V, back wire and side wire, AFCI, white, brass, tamper resistant, PVC, 5-15R, two-pole, three-wire, grounding



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton slim AFCI receptacle	TRAF15W
<b>UPC</b>	<b>Product Length/Depth</b>
032664022517	1.37 in
<b>Product Height</b>	<b>Product Width</b>
4.19 in	1.7 in
<b>Product Weight</b>	<b>Certifications</b>
0.24 lb	cULus Listed

## Product specifications

### Device type

Receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Circuit interrupter type

AFCI

### Contact material

Brass

### Features

Tamper resistant

### Application

Residential  
Commercial

### Wiring method

Back and side wire

### Allowable wire size

#14 - 10 AWG

### NEMA configuration

5-15R

### Torque rating

16 lbf-inch

### Environmental conditions

Tamper resistant

### Mounting method

Flush

### Color

White

### Face/body material

PVC  
Polycarbonate

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Installation instructions

[AFCI instruction sheet](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Tamper Resistant Slim AFCI Spec Sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)