

MT217



### #1 Square 3" Cushion Grip Screwdriver (USA)

★★★★★ 5.0 (5)

Our Milwaukee® Cushion Grip Screwdrivers (USA) are manufactured to give the professional the best-fitting screwdriver with max grip. Our screwdriver tips are custom machined to deliver a precise fit and reduce stripping during demanding fastening applications. For added confidence, the tips are laser etched to increase the gripping surface. Manufactured with high-strength boron-infused steel for increased hardness, our screwdrivers stand up to the demands of the site with ultimate durability and life. Providing increased versatility, select screwdrivers include a wrench-ready bolster for added torque and a knurled shank for precision control. Quick identification markings on the handle make it easy to identify screwdriver tip size and type, including Phillips, cabinet, ECX, slotted, and square. The demolition screwdrivers also include a hammer-ready strike cap. Our screwdrivers range in shank sizes from 3-inch to 10-inch. Our Milwaukee Cushion Grip Screwdrivers (USA) are made in the USA with best-in-class manufacturing technology and USA-sourced materials all backed by a complete Lifetime Guarantee.

#### KEY FEATURES

#### SPECIFICATIONS

#### REVIEWS

- ✓ Hammer Ready Strike Cap (select models)
- ✓ Precision Control Knurled Shank (select models)
- ✓ Available Tip Types: Cabinet, ECX, Phillips, Slotted, and Square
- ✓ Lifetime Guarantee
- ✓ Visible ID Markings
- ✓ Wrench Ready Bolster (select models)
- ✓ Available Shank Lengths: 3-inch to 10-inch
- ✓ Made in USA with USA sourced materials

#### PRODUCT SPECIFICATIONS

Material Composition	Metal Plastic
Length	6.7 in
Weight	0.125 lb
Height	1.1 in
Width	1.1 in

Bit Type	Square - Standard
Shank Length	3"
Screwdriver Type	Standard
Bit Size	#1