

Eaton XTCF020B00A

Catalog Number: XTCF020B00A

Eaton XT IEC contactor, 20A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 20A, Frame B, 45 mm, 50-60 Hz, 1, 2/3, 3, 10, 10 hp (1/3PH @115, 230/200, 230, 460, 575 V), Four-pole, , Screw terminals, FVNR



General specifications

Product Name

Eaton XT IEC contactor

EAN

4015082769673

Product Height

2 in

Product Weight

0.48501698 lb

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Number

XTCF020B00A

Product Length/Depth

2.75 in

Product Width

3 in

Compliances

RoHS Compliant
CE Marked

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

20A

HP rating - max

1, 2/3, 3, 10, 10 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Four-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

0 NO, 0 NC

Continuous ampere rating

20 A

Series

XT IEC

Operation

Non-reversing

Resources

Drawings

[XTCF_B 3D Inventor](#)

[XTCF_B 2D Drawing Xchange](#)

[XTCF_B AutoCAD 2D Footprint](#)

[XTCF_B 2D PDF](#)

[XTCF_B 3D Model Xchange](#)

[XTCF_B AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCF020B00A](#)

[Global Data Sheet - XTCF020B00A](#)