



PRODUCT-DETAILS

# MTV18-BS

## VINYL BUTT SPLICE, 22-16



General Information	
Extended Product Type	MTV18-BS
Product ID	7TBI029550R0096
Catalog Description	VINYL BUTT SPLICE, 22-16
Long Description	Vinyl Insulated Butt Splice Terminal Wire Range 22-16

Ordering	
UPC	67396012185
Country of Origin	Taiwan (Chinese Taipei)
Selling Unit of Measure	each

Container Information	
Package Level 1 Units	25 EA
Package Level 1 Width	0.254 mm 0.01 in
Package Level 1 Height	0.254 mm 0.01 in

Package Level 1 Depth / Length	0.254 mm 0.01 in
Package Level 2 Units	1000 EA
Package Level 2 Width	25.4 mm 1 in
Package Level 2 Height	25.4 mm 1 in
Package Level 2 Depth / Length	25.4 mm 1 in

---

### Additional Information

Brand / Label	Sta-Kon
Color	Red
Effective Date	20010404
Material	Vinyl
Product Name	"TERMINALS, ELECTRICAL SPLICES"
Product Type	Vinyl Insulated Butt Splice
Sub Brand / Label	Marrette
Voltage Rating	600 V
Wire Size	22-16 AWG

---

### Certificates and Declarations

Data Sheet, Technical Information	MTV18-BS
-----------------------------------	----------

---

### External Classifications and Standards

UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

