



PRODUCT-DETAILS

# MTV14-BS

## VINYL BUTT SPLICE, 16-14



### General Information

Extended Product Type	MTV14-BS
Product ID	7TBI029550R0081
Catalog Description	VINYL BUTT SPLICE, 16-14
Long Description	Vinyl Insulated Butt Splice Terminal Wire Range 16-14

### Ordering

UPC	67396012178
Country of Origin	Taiwan (Chinese Taipei)
Selling Unit of Measure	each

### Container Information

Package Level 1 Units	25 EA
Package Level 1 Width	0.254 mm 0.01 in
Package Level 1 Height	0.254 mm 0.01 in

Package Level 1 Depth / Length	0.254 mm 0.01 in
Package Level 2 Units	1000 EA
Package Level 2 Width	25.4 mm 1 in
Package Level 2 Height	25.4 mm 1 in
Package Level 2 Depth / Length	25.4 mm 1 in

---

### Additional Information

Brand / Label	Sta-Kon
Color	Blue
Effective Date	20010404
Material	Vinyl
Product Name	"TERMINALS, ELECTRICAL SPLICES"
Product Type	Vinyl Insulated Butt Splice
Sub Brand / Label	Marrette
Voltage Rating	600 V
Wire Size	16-14 AWG

---

### Certificates and Declarations

Data Sheet, Technical Information	MTV14-BS
-----------------------------------	----------

---

### External Classifications and Standards

UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

