

Project Name

Location

Prepared By



## SATCO S28737

20WA21/LED/3CCT/120-277V

### Notes

(www) 01-22-2023 03:00:43

### General

Status	Active
Watts	20W
Incandescent Equivalent	150W
Volts	120V-277V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	80
Lumens	2760L/3020L/2860L
Beam Spread	280
Dimmable	Yes-Dimmable
Hours Rated	50000
Product Category	Type A
Technology	LED
Min Compartment Size	Length: 6 in. Width: 6 in. Height: 8.5 in.
Ballasting Requirements	Ballast Bypass; Direct wire 120-277V line voltage; No ballast or external driver required

### Electrical

Operating Frequency	50/60Hz
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Dimming Note	120V only
Power Factor	>0.9
Surge Protection	Built-in surge protection - 2KV
Operating Temperature	-25C (-13F) to +45C (+113F)

### Physical

MOL	5.08
MOD	2.46
Lens Finish	Frosted
Lens Material	Polycarbonate (PC)
Housing Color	White
Weight (lb.)	0.44

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes