

# Eaton GFH15RD

Catalog Number: GFH15RD

Eaton HG GFCI, 15A, 125V, Red, Slim



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton hospital grade GFCI receptacle	GFH15RD
UPC	Product Length/Depth
032664022906	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Certifications
0.01 lb	cULus Listed

## Product specifications

### Device type

Receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Circuit interrupter type

GFCI

### Contact material

Brass

### Application

Residential  
Commercial

### Wiring method

Back and side wire

### Allowable wire size

#14 - 10 AWG

### NEMA configuration

5-15R

### Torque rating

16 lbf-inch

### Mounting method

Flush

### Color

Red

### Face/body material

Nylon  
Polycarbonate

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Installation instructions

[Installing and testing a GFCI receptacle instruction sheet](#)

### Multimedia

[What is a Ground Fault Circuit Interrupting \(GFCI\) receptacle?](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)