

Eaton GFH20V

Catalog Number: GFH20V

Eaton HG GFCI, 20A, 125V, Ivory, Slim



General specifications

Product Name	Catalog Number
Eaton hospital grade GFCI receptacle	GFH20V
UPC	Product Length/Depth
032664022944	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Certifications
0.01 lb	cULus Listed

Product specifications

Device type

Receptacle

Amperage Rating

20A

Voltage rating

125V

Circuit interrupter type

GFCI

Contact material

Brass

Application

Residential

Commercial

Wiring method

Back and side wire

Allowable wire size

#14 - 10 AWG

NEMA configuration

5-20R

Torque rating

16 lbf-inch

Mounting method

Flush

Color

Ivory

Face/body material

Polycarbonate

Nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Installation instructions

[Installing and testing a GFCI receptacle instruction sheet](#)

Multimedia

[What is a Ground Fault Circuit Interrupting \(GFCI\) receptacle?](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)