

Eaton GFD20W

Catalog Number: GFD20W

Eaton slim blankface GFCI receptacle, self-test, #14 - 10 AWG, 20 A, residential, commercial, flush, 125 V, back and side wire, white, brass, Blankface, thermoplastic, two-pole, three-wire, grounding



General specifications

Product Name	Catalog Number
Eaton slim blankface GFCI receptacle	GFD20W
UPC	Product Length/Depth
032664022814	1.03 in
Product Height	Product Width
4.19 in	1.69 in
Product Weight	Certifications
0.19 lb	cULus Listed NOM

Product specifications

Device type

Blankface
Receptacle

Type

Self-test

Amperage Rating

20A

Voltage rating

125V

Circuit interrupter type

GFCI

Contact material

Brass

Application

Residential
Commercial

Wiring method

Back and side wire

Allowable wire size

#14 - 10 AWG

NEMA configuration

5-20R

Torque rating

16 lbf-inch

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Color

White

Face/body material

PVC
Thermoplastic

Resources

Specifications and datasheets

Tamper resistant slim GFCI receptacles spec sheet

Controlled slim GFCI spec sheet

Standard slim GFCI spec sheet

GFCI Cross Reference

Tamper and weather resistant slim GFCI receptacles spec sheet

Slim Blankface GFCI Receptacles Spec Sheet

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)