

Specification Sheet

Part Number: 2.5NFP9C



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Natural, 100 ft/roll

Article Number 161-05027

Type 2.5NFP

Color Natural (NA)

Quantity Per reel

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Natural, 100 ft/roll

Global Part Name 2.5NFP-PE-NA

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	7.92
Bundle Diameter Max (Imperial)	3
Bundle Diameter Max (Metric)	76.2
Diameter D (Imperial)	0.375
Diameter D (Metric)	9.53
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	9.53
Wall Thickness WT (Imperial)	0.052
Wall Thickness WT (Metric)	1.32
Material	Polyethylene (PE)
Material Shortcut	PE

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)