

Specification Sheet

Part Number: MB4SHA10H4

For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.

A predrilled hole extends mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 500/pkg

Article Number 151-29206

Type MB4SHA

Color White (WH)

Quantity Per bag

Product Description MB4SHA adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have a predrilled hole to extend mounting options.

Short Description Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 500/pkg

Global Part Name MB4SHA-PA66-WH

Length L (Imperial) 1.12

Length L (Metric) 28.3

Fixation Method Adhesive

Width W (Imperial) 1.12

Width W (Metric) 28.3

Cable Ties T18 - T50

Height H (Imperial) .23

Height H (Metric) 5.8

Cable Tie Width Max (Imperial) 0.18

Cable Tie Width Max (Metric) 4.6

Mounting Hole Diameter D (Imperial) 0.15

Mounting Hole Diameter D (Metric) 3.9 mm

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)