

Specification Sheet

Part Number: T120S0PPH4



Polypropylene cable ties deliver excellent resistance to chemicals and salts.

Inside serrations provide strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Heavy Duty Cable Tie, 9" Long, 60lb Tensile Strength, PP, Black, 500/pkg

Article Number 111-12827

Type T120S

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's polypropylene cable ties offer added resistance to most chemicals. T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 9" Long, 60lb Tensile Strength, PP, Black, 500/pkg

Global Part Name T120S-PP-BK

Minimum Tensile Strength (Imperial) 60

Minimum Tensile Strength (Metric) 267

Length L (Imperial) 9.0

Length L (Metric) 225.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.30

Width W (Metric) 7.6

Bundle Diameter Min (Imperial) 0.5

Bundle Diameter Min (Metric) 12.7

Bundle Diameter Max (Imperial) 2.17

Bundle Diameter Max (Metric) 55.0

Thickness T (Imperial) 0.06

Thickness T (Metric)	1.6
Cable Tie Head Length (Imperial)	0.39
Cable Tie Head Width (Imperial)	0.52
Height H (Metric)	7.7
Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)