



Catalog Number
Notes
Type

Contractor Select™

FMLWL ALO

Color and Lumen Switching,
Linkable Low Profile LED Wrap



An all-in-1, low-profile, linear and narrow wraparound with 9 possible color/lumen configurations standard. Comes with decorative endcaps with integrated linkability and a frosted diffuser providing widespread, uniform illumination. Ideal for many applications including corridors, kitchens, breakrooms, utility work areas and stairways.

FEATURES:

- Adjustable Lumen Output: 2000LM, 3000LM, 4000LM
- 3 CCT Switchable: 3000K, 4000K, 5000K
- Linkable: Connect up to 6 fixtures end to end from a single power drop. All fixture lumens and CCT behave independently
- Operates at 120V, 60Hz Non-Dimming
- All versions are rated for 50,000 hours life



Catalog Number	UPC	Description	Linkable	Lumens	CRI	Color Temperature	Input Watts	Voltage	Pallet qty.
FMLWL LNK 48 ALO4 8SWW2	00194995061037	4' LED Wrap	LNK	2,000 - 4,000	80 CRI	3000K/4000K/5000K	25-55W	120V	96

More configurations are available. [Click here](#) or visit www.acuitybrands.com and search for FMLWL

Replacement Parts and Accessories	
DFMLWL48	4' white acrylic diffuser
LNK CORD M100	18" Linking Cord
RK2FMLWL HK2 M100	Replacement Hardware Kit

Performance Data

	2000LM			3000LM			4000LM		
	Lumen	Watt	LPW	Lumen	Watt	LPW	Lumen	Watt	LPW
3000K	2241	26	88	3268	40	83	4009	55	74
4000K	2469	25	101	3562	38	96	4515	53	87
5000K	2372	26	93	3347	40	85	4120	55	75



Specifications

INTENDED USE:

Provides an LED lighting platform to deliver general ambient lighting for surface-mount ceiling applications. Light engine delivers long life and excellent color to ensure a quality, low-maintenance light installation. Ideal for use in closets, foyers, hallways, corridors, bedrooms, offices, utility work areas, and more.

CONSTRUCTION:

The LED wrap is constructed of a metal housing with decorative plastic end caps. The white frosted diffuser provides even illumination and softens the appearance of the LEDs for improved aesthetics.

OPTICS:

4' produces 2,000 to 4,000 lumens. All versions are rated for 50,000 hours life. Thermal formed diffuser is of highly transmissive material to minimize lamp image and provides high-angle brightness control. One piece contemporary design wrap around diffuser softens appearance for improved aesthetics.

ELECTRICAL:

Long-life LEDs, coupled with a high-efficiency driver, provide superior illumination for extended service life. 70% LED lumen maintenance at 60,000 hours (L70/60,000).

LISTINGS:

UL certified to US and Canadian standards. Listed for damp locations.

WARRANTY:

5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at:

www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Dimensions

4'

Length: 47-2/5 (120.4)

Width: 5-1/2 (14.0)

Depth: 2-3/5 (6.6)

Weight: 5lbs (1.0kg)

All dimensions are inches (centimeters) unless otherwise indicated.

