









Juno® Canless















Canless downlights are installed directly into the ceiling which eliminates the need for traditional recessed housings. These IC rated fixtures possess a slim profile that allows for them to install safely and securely into as little as 2" of plenum. No need to purchase a housing, trim, and lamp anymore, simply purchase a canless product for a cost efficient solution. Juno® canless solutions provide an array of product families including: Wafers, Podz, and 1" and 2" LED downlights.




















	Application	Size	Trim Style	Lumen	CCT	CRI	Voltage	Dimming	Install Type	Finishes	Special Applications	
Wafers												
 <p>Flat, Switchable WF4 WF6 WF8</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	4"	Flat, Modern Aesthetic	670	Switchable White 2700K- 5000K	90	120V	Dimmable to 10% only with Triac Dimmers	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White Black Brushed Nickel Oil Rubbed Bronze		
		6"		950								
		8"		1600								
 <p>Flat, Switchable & ALO WF2 WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	2"	Flat, Modern Aesthetic	Adjustable Lumens 500 675 850	Switchable White 2700K- 5000K	90	120V	Dimming 100% to 10% with most Standard Incandescent Dimmers	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White Color Finished Trim Inserts Available		
		4"		Adjustable Lumens 700 900 1100								120V Or MVOLT Multi-Volt (120-277)
		6"		Adjustable Lumens 800 1050 1300								120V Or MVOLT Multi-Volt (120-277)
 <p>Regressed, Switchable WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	4"	Regressed, Traditional Aesthetic	670	Switchable White 2700K- 5000K	90	120V	Dimming 100% to 10% with most Standard Incandescent Dimmers	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White		
		6"		950								
 <p>Deep Regressed Baffle, Switchable & ALO WF2 WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	2"	Deep Regressed Baffle, Traditional Aesthetic	Adjustable Lumens 525 700 900	Switchable White 2700K- 5000K	90	120V	Dimming 100% to 10% with most Standard Incandescent Dimmers	Canless Installs directly into ceiling drywall 3" of plenum space needed	Matte White Color Finished Trim Inserts Available		
		4"		Adjustable Lumens 700 900 1100								
		6"		Adjustable Lumens 967 1091 1123								



	Application	Size	Trim Style	Lumen	CCT	CRI	Voltage	Dimming	Install Type	Finishes	Special Applications
Wafers											
 <p>Deep Regressed Smooth, Switchable & ALO WF2 WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	2"	Deep Regressed Smooth, Traditional Aesthetic	Adjustable Lumens 525 700 900	Switchable White 2700K-5000K	90	120V	Dimming 100% to 10% with most Standard Incandescent Dimmers	Canless Installs directly into ceiling drywall 3" of plenum space needed	Matte White Color Finished Trim Inserts Available	
		4"		Adjustable Lumens 700 900 1100							
		6"		Adjustable Lumens 800 1050 1300							
 <p>Adjustable, Switchable WF4 WF6</p>	Indoor Single Family Multi-Family Light Commercial Perfect for sloped ceilings	4"	Adjustable, Modern Aesthetic	850	Tunable White 2700K-5000K	90	120V	Dimming down to 10% with most Standard Incandescent Dimmers	Canless Installs directly into ceiling drywall 3" of plenum space needed	Matte White Matte Black	
		6"		1000							
 <p>Smart, Flat WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	4"	Flat, Modern Aesthetic	650	Tunable White 2700K-5000K	90	120V	Dimmable to 1% (Not for use with wall dimmers). Perfect for use as a nightlight	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White	
		6"		950							
 <p>Smart, Regressed WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	4"	Regressed, Modern Aesthetic	640 - 680	Tunable White 2700K-5000K	90	120V	Dimmable to 1% (Not for use with wall dimmers). Perfect for use as a nightlight	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White Black Brushed Nickel Oil Rubbed Bronze	
		6"		944 - 992							
 <p>Smart, Adjustable WF4 WF6</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial	4"	Adjustable, Modern Aesthetic	770 - 825	Tunable White 2700K-5000K	90	120V	Dimmable to 1% (Not for use with wall dimmers). Perfect for use as a nightlight	Canless Installs directly into ceiling drywall 2" of plenum space needed	Matte White	
		6"		1085 - 1170							
Podz (Round & Square) JPDZ											
 <p>Round & Square Podz JPDZ</p>	Indoor/Outdoor Single Family Multi-Family Light Commercial New Construction & Remodel	4" 5" 6"	Regressed, Traditional Baffle or Smooth Aesthetic Options	Adjustable Lumen Output 700 1000 1200	Switchable White 2700K-5000K plus WarmDim	90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 4" of plenum space needed	Black Clear Haze Wheat Haze White	



	Application	Size	Trim Style	Lumen	CCT	CRI	Voltage	Dimming	Install Type	Finishes	Special Applications
2" LED Downlights (Round & Square) 2LED											
 2 LED Round Cone	Indoor Single Family Multi-Family Light Commercial New Construction or Remodel	2"	Regressed, Smooth Traditional Aesthetic	600 1000	2700K 3000K 3500K 4000K	80 90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 5.5" of plenum space needed	Black Clear Haze Wheat Haze White	
 2 LED Round Baffle	Indoor Single Family Multi-Family Light Commercial New Construction or Remodel	2"	Regressed, Baffle Traditional Aesthetic	600 1000	2700K 3000K 3500K 4000K	80 90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 5.5" of plenum space needed	Black Bronze Satin Nickel White	
 2 LED Round Adjustable	Indoor Single Family Multi-Family Light Commercial New Construction or Remodel	2"	Adjustable, Low profile gimbal Modern Aesthetic	600 1000	2700K 3000K 3500K 4000K	80 90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 5.5" of plenum space needed	Black Bronze Satin Nickel White	
 2 LED Square Downlight	Indoor Single Family Multi-Family Light Commercial New Construction or Remodel	2"	Regressed, Square Traditional Aesthetic	600 1000	2700K 3000K 3500K 4000K	80 90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 5.5" of plenum space needed	Black Bronze Satin Nickel White	
 2 LED Square Adjustable	Indoor Single Family Multi-Family Light Commercial New Construction or Remodel	2"	Square Adjustable, Low profile gimbal Modern Aesthetic	600 1000	2700K 3000K 3500K 4000K	80 90	120V Or MVOLT Multi-Volt (120-277)	Dimming 100% to 5% with use of forward, reverse phase or 0-10V Dimmers	Canless Installs directly into ceiling drywall 5.5" of plenum space needed	Black Bronze Satin Nickel White	
Mini MD1LG2											
 Round MD1LG2 RD	Indoor/Outdoor Single Family Multi-Family Light Commercial	1"	Regressed, Smooth Traditional Aesthetic	300	2700K 3000K 3500K 4000K	80 90	Class 2, 120V to 12V AC transformer required	May be dimmed with dimmers tested and qualified by Juno for use with TL602E and MAGXFMR transformers	Canless Installs directly into ceiling drywall 4" of plenum space needed	Black Bronze Satin Nickel White	
 Square MD1LG2 SQ	Indoor/Outdoor Single Family Multi-Family Light Commercial	1"	Regressed, Smooth Traditional Aesthetic	300	2700K 3000K 3500K 4000K	80 90	Class 2, 120V to 12V AC transformer required	May be dimmed with dimmers tested and qualified by Juno for use with TL602E and MAGXFMR transformers	Canless Installs directly into ceiling drywall 4" of plenum space needed	Black Bronze Satin Nickel White	
 Adjustable, Round MG1LG2 RD	Indoor Single Family Multi-Family Light Commercial	1"	Adjustable, Round Modern Aesthetic	300	2700K 3000K 3500K 4000K	80 90	Class 2, 120V to 12V AC transformer required	May be dimmed with dimmers tested and qualified by Juno for use with TL602E and MAGXFMR transformers	Canless Installs directly into ceiling drywall 4" of plenum space needed	Black Bronze Satin Nickel White	
 Adjustable, Square MG1LG2 SQ	Indoor Single Family Multi-Family Light Commercial	1"	Adjustable, Square Modern Aesthetic	300	2700K 3000K 3500K 4000K	80 90	Class 2, 120V to 12V AC transformer required	May be dimmed with dimmers tested and qualified by Juno for use with TL602E and MAGXFMR transformers	Canless Installs directly into ceiling drywall 4" of plenum space needed	Black Bronze Satin Nickel White	

Notes:
 1. Wet Location is an ordering OPTION for the round and square mini downlights.
 2. Mini LED fixtures require an electronic/magnetic transformer (sold separately) to operate