



High Tension Hacksaw



The Klein Tools 12-Inch (30 cm) High Tension Hacksaw has adjustable blade tension up to 30,000 pounds per square Inch for fast, precise cuts. Easily convert hacksaw into jab saw with reciprocating blade mount, completely tool-free. The hacksaw also offers convenient storage in-frame for extra blades.

Specifications

Type:	High Tension	Application:	Metal; Plastic; PVC; PEX; ABS Pipes; Wood
Special Features:	Reciprocating Blade Mount, In Frame Blade Storage, 45 and 90 Degree Blade Mounts	Teeth Per Inch:	24
Blade Length:	12" (30.5 cm)	Overall Length:	18.5" (47 cm)
Overall Height:	1.25" (3.2 cm)	Overall Width:	5.8" (14.7 cm)
Material:	Steel, Plastic, TPR Overmold	Blade Material:	Bi-Metal
Blade Finish:	Painted and Screen Printed Black	Blade Thickness:	0.02" (0.05 cm)
Throat Depth:	5.7" (14.5 cm)	Frame Material:	Steel
Handle Material:	Aluminum, TPR Overmold	Handle Length:	5.8" (14.7 cm)
For Use On:	Metal; Plastic; PVC; PEX; ABS Pipes; Wood	Weight:	2 lb (0.9 kg)