

AC Line Splitter with GFCI Tester

The Rack-A-Tiers AC Splitter features a receptacle and GFCI tester as well as the ability to measure the current through the measuring rings. Verify your receptacle wiring, measure voltage and use your clamp meter (not included) to measure current up to 15A.

The AC Splitter is equipped with lights that show 5 different wiring faults: Open Ground, Open Neutral, Hot/Ground Reverse, Open Hot, Hot/Neutral Reverse.

#99020

Voltage measurement ring

Current measurement ring (x10 and x1)

GFCI button

Socket connection indicators

Current maximum: 15A

Input voltage: 120V

cETLus listed

Lights display 5 wiring faults

Designed for receptacles with ground up or ground down installation

