

Weather Proof Cover - Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Black

Item WP7000BL



PRODUCT DESCRIPTION

Extra-Duty Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ▶ 100% Paintable surface.
- ▶ Complies with 2020 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications.
- ▶ CEC Article 26-702 compliant.
- ▶ UL Certified for type 3R outdoor enclosures.
- ▶ Meets requirements for cold impact testing: -60° F (-51° C).
- ▶ Heavy-duty UV stabilized polycarbonate cover, mounting base, and inserts.
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws.
- ▶ Lockable hasp: All models accept up to 0.19" dia shank.
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact.
- ▶ Reinforced hinge pin designed to exceed 40 lbf. hinge hang/stress test.

APPLICATIONS

- ▶ Receptacle Protection

TECHNICAL DATA

General

Model Number	WP7000BL
Description	Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Black
UPC Code	078275159143
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

Mechanical Specifications

Number of Included Inserts	2
Hinge Direction	Vertical/Horizontal
Is Extra-Duty Rated	Yes

Dimensions

Lockable Hasp Maximum Diameter (in)	0.19
Lockable Hasp Maximum Diameter (mm)	4.8
Product Dimensions (H x W x D) in	5.5 x 3.75 x 1.5 in
Expandable Depth Mm	54
Expandable Depth In	2 1/8
Accepted Cord Size Max	1x16 AWG
Box Type	Single

Material Specifications

Color	Clear; Black
Weatherproof Cover Material	UV Stabilized Plastic

Packaging

Shipping Weight (lbs)	0.35
Unit Carton Dimensions (H x W x L) in	1.5 x 3.7 x 5.5 in
Product Weight (kg)	0.159
Product Weight (lbs)	0.35

Standards and Certifications

UL Certification	cULus
California Proposition 65	None
RoHS Certification	Y