

Model Name	VarianRS40 (EVC27)
Rated Input Voltage	200-240 VAC
Max Rated Output Current	40A
AC Power Frequency	60 Hz
Input Protection	Undervoltage, Overvoltage, Residual Current, Surge, Ground Fault
Output Protection	Over Current, Over Temperature, Control Pilot Fault
Weather Protection	IP65
Charging Interface	SAE J1772 Compliant, Type 1 Plug
Protection	IP65
Operation Temperature	-30°C~50°C
Relative Humidity	Up to 95% non-condensing
Connectivity	OCPP 1.6 J
Network	Ethernet / Wi-Fi
Certification	ETL
Cable Length	25ft
Installation Type	Wall-Mounted
Authentication	RFID ISO14443
Status Indication	Red, Green, Blue LED
Product Dimensions	8.6" x 8.6" x 3.7"
Package Dimensions	16" x 12" x 8.75"



Variablegrid Adaptive Power Inc.

969 W 1st St
North Vancouver, BC V7P 1A4
1-800-645-2314

Email us today at
info@variablegrid.com
www.variablegrid.com