



Pass and Seymour
30A 125/250V 10-30R Straight Blade Single Flush Receptacle, 3-Pole, 3-Wire
Part No. 3860



Straight Blade Receptacle 30A 125/250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

| | | | |
|-------------------|----------------|------------|--------------|
| Product Line | Pass & Seymour | UPC Number | 785007793208 |
| Country Of Origin | China | Standard | UL 498 |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 2.5 in | Product Depth US | 1.9 in |
| Product Height US | 3.75 in | | |

Technical Information

| | | | |
|------------|------------|-----------------|-------|
| Connection | Non Ground | Number of Wires | 3 |
| Amperage | 30 A | Number of Poles | 3-Way |
| Wire Size | 4 | | |