3611 Commercial Street T. 604.872.5503 **IP53-RDC3SD** 0;; F. 604.872.5560 Vancouver, BC V5N 4G1


Project:	Туре:	QTY:
Product Code:		



Product Code IP53-RDC3SD-TRIM COLOR - REFLECTOR COLOR -LAMP **VOLTAGE** -**OPTIONS** W*=white WC =white cone WW27 =2700K 120=120VAC 125TCA =1.25" thick A =aluminum SC*=mat silver cone WW30*=3000K ceiling В =black BC =black cone DTW322=dim to warm adaptor CC =custom color 3000K→2200K RDC3TP*1=mounting template * Components usually in-stock for guick assembly and shipping.

- 120V line voltage dimmable with most dimmers
- Short circuit and overheat protected, RoHS compliant
- Driver box accommodate up to 4 No.12 AWG wires
- Ceiling recessed mount
- Optional mounting plate

Installation Hole Size: Ø3"



RoHS

- Entire LED engine sealed off by clear tempered glass lens
- 2700K, 3000K CCT + Dim To Warm lamp color

Electrical System:

- Constant current drive technology
- HPF, high efficiency designs, 7W system watt

Certified to CSA C22.2 No.250.0 Conformed to UL 1598 Certification Marks (where applicable) will be found on our luminaires and its components

Datecode 20190418

