



On-Q
4K Premium High Speed HDMI™ Cable, 1m
Part No. AC4K1MBK

4K PREMIUM HIGH SPEED
HDMI™ CABLE



Experience unparalleled video and audio quality with our 4K Premium Certified HDMI Cable. This 2-meter cable supports 4K resolution at 60Hz, ensuring crystal-clear visuals and immersive sound. Each cable is in-wall rated (CL3/FT4) for safe installation and supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD, and Dolby Atmos®. The gold-plated connectors resist corrosion and provide the highest level of signal conductivity. Each cable bears the Premium Certification label to guarantee authenticity. The 10-pack comes in a box with individually bagged cables inside.

Features & Benefits

Supports 4K at 60Hz

CL3/FT4 Rated for in-wall use

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Specifications

General Info

Product Line	On-Q	Color	Black
Finish	Matte	UPC Number	804428434955
Country Of Origin	China		

Dimensions

Product Width US	0.87 in	Product Weight US	0.18 lb
Product Height US	10.16 in	Product Length US	7.09 in

Technical Information

Wire Gauge	16 AWG, 22 AWG, 29 AWG	Video Resolution	4K 60Hz
Jacket Application	In-Wall Rated	Cable Type	Premium HDMI

Jacket Rating	CL3 Rated, FT4 Rated	Data Transfer Rate	18 Gbps
Connector Type	HDMI, Power, RJ-25C	Input Voltage	12 to 20 VDC, 120/230/240/277 VAC, 347 V
Video Input Support	HDMI	Conductor Material	Gold
Environmental Conditions	0.9		
