

Data Sheet | Item Number: 811-471

Supply module; 35 mm²; for 811 Series Fuse Terminal Blocks; SCREW CLAMP CONNECTION; 35,00 mm²; light gray

<https://www.wago.com/811-471>



Color:  light gray

Supply module, 811 Series, light gray

Easily, quickly and safely connect conductors with this supply module (item number 811-471). Ensure that the strip lengths are 14 mm when connecting conductors to this supply module. This product features conductor terminals and utilizes a screw connection. Depending on the type of conductor, this supply module is ideal for conductor cross sections ranging from 6 mm² to 35 mm².

Electrical data

Ratings per IEC/EN		Ratings per IEC/EN 2	
Nominal voltage (III/3)	600 V	Rated voltage (III/3)	1000 V

General information

Voltage type 1	AC
Voltage type 2	DC

Connection data

Number of levels	1
Connection 1	
Connection technology	Screw connection
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	6 ... 35 mm² / 10 ... 2 AWG
Stranded conductor	6 ... 35 mm² / 10 ... 2 AWG
Fine-stranded conductor	4 ... 25 mm² / 12 ... 4 AWG
Fine-stranded conductor; with insulated ferrule	4 ... 25 mm² / 12 ... 4 AWG
Strip length	14 mm / 0.55 inches



Mechanical data	
Torque	4 Nm

Material data	
Note (material data)	Information on material specifications can be found here
Color	light gray
Fire load	0 MJ
Weight	20 g

Commercial data	
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 9.0	EC002848
ETIM 8.0	EC002848
PU (SPU)	16 (4) pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821838654
Customs tariff number	85369010000

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption