

Specifications



Eaton TRAG15W

Eaton slim AFGF receptacle, tamper resistant, self-test, #14 - 10 AWG, 15 A, residential, commercial, flush, 125 V, AFGF, back and side wire, white, brass, polycarbonate, 5-15R, two-pole, three-wire, grounding

General specifications

PRODUCT NAME	Eaton slim AFGF receptacle
CATALOG NUMBER	TRAG15W
UPC	032664022685
PRODUCT LENGTH/DEPTH	1.37 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.24 lb
CERTIFICATIONS	NOM cULus Listed CSA Certified UL Listed

Product specifications	
DEVICE TYPE	Receptacle
TYPE	Self-test
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CIRCUIT INTERRUPTER TYPE	AFGF
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant
APPLICATION	<ul style="list-style-type: none"> • Residential • Commercial
WIRING METHOD	Back and side wire
ALLOWABLE WIRE SIZE	#14 - 10 AWG
NEMA CONFIGURATION	5-15R
TORQUE RATING	16 lbf-inch
ENVIRONMENTAL CONDITIONS	Tamper resistant
MOUNTING METHOD	Flush
COLOR	White
FACE/BODY MATERIAL	PVC Polycarbonate
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources	
INSTALLATION INSTRUCTIONS	Installing and testing an AF/GF receptacle
MULTIMEDIA	Ground Fault Circuit Interrupter (GFCI) demonstration
SPECIFICATIONS AND DATASHEETS	Tamper Resistant Slim AF/GF Spec Sheet

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:

Reserved.

